

90560 L & R

Technische Daten:

- Eingangsspannung: 9V – 32V DC
- Steckertyp: DT04-6P
- Vollbelegt
- Kabellänge: 80cm
- Gewicht: 1720g
- Größe: Höhe 201mm Breite 214mm
- Befestigung: M12 Schrauben
- Zulassung: E24
- Arbeitstemperaturbereich: -50° bis +80°
Celsius

Funktion:

- Abblend-, Fern-, Blink-, Standlicht
- Blinklicht vorne und hinten
- Im Winkel verstellbar

Pin Belegung DT04-6P:

Pin	Kabelfarbe	Funktion
6	Weiß	Masse
5	Braun	Abblendlicht
4	Rot	Fernlicht
3	Blau	Standlicht
2	Schwarz	Blinklicht
1	Weiß	Masse

Beschreibung:

Das Gehäuse besteht aus Aluminium. Die Lampe kann auf 2 Arten befestigt werden. Bei der Montage der Lampe, sind die Vorgaben der StVZO zu beachten.

90560 L & R

Technical specifications:

- Input voltage: 9V – 32V DC
- Plug type: DT04-6P
- Cable length: 80cm
- Weight: 1720g
- Size: height 201mm width 214mm
- Attachment: M12 screw
- Authorization: E24
- Temperature range: -50° bis +80° Celsius

Function:

- Dimmed headlights, low beam, high beam, turn signal
- Turnsignal in the front and back
- Angle adjustable

Pin assignment DT04-6P:

Pin	Cable color	Function
6	White	Ground
5	Brown	Low beam
4	Red	High beam
3	Blue	Parking light
2	Black	Turn signal
1	White	Ground

Description:

The casing is made out of aluminum. You can attach the lamp in 2 ways. After the mounting, please check your local regulation.