Výtah z online katalogu

G 5/ 2 DIO SO BU

Obj.č.:: 3022247

Obrázek ukazuje kombinaci z variant G 5/2, G 5/3 a G 5/4



http://eshop.phoenixcontact.cz/phoenix/treeViewClick.do?UID=3022247

Průchozí svornice, Způsob připojení: Šroubové připojení, Průřez:0,2 mm² - 4 mm², AWG: 24 - 12, Šířka: 20 mm, Výška: 24 mm, Barva: modrá, Způsob montáže: Přímé přišroubování

Údaje	
EAN	4 017918 384920
Balení	50 ks
Celní tarif	85369010
Váha brutto v kusech	0,01546 kg

Poznámky k produktu

WEEE/RoHS-compliant since: 01.01.2005

http://www.download.phoenixcontact.com
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Certifikáty/Osvědčení

Aprobace: GOST

Vyžádané aprobace:

Aprobace z:

Adresa

PHOENIX CONTACT, s.r.o.
Dornych 47
617 00 Brno,Czech Republic
Telefon +420 542 213 401
Fax +420 542 213 701
http://www.phoenixcontact.cz

© 2013 Phoenix Contact
Technické změny vyhrazeny.