



Rozpěrka, posunout výš o V=25 mm

Typ **HS25-CI**
 Catalog No. **002291**

Dodavatelský program

Product range		CI insulated enclosures
Příslušenství		příslušenství pro vestavné systémy
funkce		k nastavení vestavných systémů do větší výšky
Informace k rozsahu dodávky		pro montážní plech jsou potřeba 4 kusy, pro lištu DIN 2 kusy
Increase by		25 mm

Technická data podle ETIM 7.0

Cabinet enclosures (EG000011) / Component for installation (switchgear cabinet) (EC002620)			
Elektrotechnika, automatizační technika a technika řízení procesu / Skřín, rám, konstrukce, nosic stavební skupiny / Elements for switching cabinet, housing, rack / Component for installation (electrical cabinet) (ecl@ss10.0.1-27-18-28-11 [ACN627011])			
Model			Other
Suitable for enclosure building width		mm	0
Suitable for enclosure building height		mm	0
Suitable for enclosure building depth		mm	0
Width		mm	0
Height		mm	25
Depth		mm	0
Max. load capacity		kg	40
Material			Plastic
Colour			Grey
RAL-number			7035

aprobace,

North America Certification		UL/CSA certification not required
-----------------------------	--	-----------------------------------