



Rozpěrka, posunout výš o V=50 mm

Typ **HS50-CI**  
 Catalog No. **002292**

### Dodavatelský program

|                             |  |  |  |
|-----------------------------|--|--|--|
| Product range               |  |  | CI insulated enclosures                                      |
| Příslušenství               |  |  | příslušenství pro vestavné systémy                           |
| funkce                      |  |  | k nastavení vestavných systémů do větší výšky                |
| Informace k rozsahu dodávky |  |  | pro montážní plech jsou potřeba 4 kusy, pro lištu DIN 2 kusy |
| Increase by                 |  |  | 50 mm  |

### Technická data podle ETIM 7.0

|   |  |    |         |
|---|--|----|---------|
| Cabinet enclosures (EG000011) / Component for installation (switchgear cabinet) (EC002620)  |  |    |         |
| Elektrotechnika, automatizační technika a technika řízení procesu / Skříň, rám, konstrukce, nosic stavební skupiny / Elements for switching cabinet, housing, rack / Component for installation (electrical cabinet) (ecl@ss10.0.1-27-18-28-11 [ACN627011]) |  |    |         |
| Model   |  |    | Other   |
| Suitable for enclosure building width   |  | mm | 0       |
| Suitable for enclosure building height  |  | mm | 0       |
| Suitable for enclosure building depth   |  | mm | 0       |
| Width   |  | mm | 0       |
| Height  |  | mm | 50      |
| Depth   |  | mm | 0       |
| Max. load capacity  |  | kg | 40      |
| Material  |  |    | Plastic |
| Colour  |  |    | Grey    |
| RAL-number  |  |    | 7035    |

### aprobace,

|                             |  |  |                                   |
|-----------------------------|--|--|-----------------------------------|
| North America Certification |  |  | UL/CSA certification not required |
|-----------------------------|--|--|-----------------------------------|