



Parametrizační modul pro frekvenční startéry DE1 a DE11

Typ DXE-EXT-SET
Catalog No. 174621
Alternate Catalog No. DXE-EXT-SET

Dodavatelský program

Popis		s voličem pro čas rampy a provozní režim s potenciometrem pro ochranu motoru a pevnou frekvenci
Použitelný pro		DE1, DE11
Typy svorek		Zásuvný modul (čelní)

Ověření návrhu podle ČSN EN 61439

Technické údaje pro ověření konstrukce			
Provozní teplota okolí min.		°C	-10
Provozní teplota okolí max.		°C	50

Technická data podle ETIM 7.0

Low-voltage industrial components (EG000017) / Accessories for frequency controller (EC002025)			
Elektrotechnika, automatizační technika a technika řízení procesu / Pohon elektrický / Menic kmitoctu / Static frequency converter (accessory) (ecl@ss10.0.1-27-02-31-92 [AFR303003])			
Type of accessory			Other

aprobace,

Product Standards			UL 508C; CSA-C22.2 No. 274; IEC/EN61800-3; IEC/EN61800-5; CE marking
UL File No.			E172143
UL Category Control No.			NMMS, NMMS7
CSA File No.			UL report applies to both US and Canada
North America Certification			UL recognized, certified by UL for use in Canada
Specially designed for North America			No
Suitable for			Branch circuits

Rozměry

