



Svodič přepětí třídy T1+T2 (B+C), 1pól

Typ SPBT12-280/1
Catalog No. 158306
Alternate Catalog No. SPBT12-280-1

Dodavatelský program

Výrobky		svodiče přepětí
Oblast použití		Obytná budova Průmyslová budova Volné plochy

Technická data podle ETIM 7.0

Earthing, lightning and surge protection (EG000021) / Combined arrester for power supply systems (EC001457)			
Elektrotechnika, automatizační technika a technika řízení procesu / Ochranné zařízení, přístroj / Svod přepětí / Combined lightning current/surge arrester f. power supply s. (ecl@ss10.0.1-27-13-08-08 [ACN284011])			
System configuration DC			No
System configuration IT			No
System configuration TN			Yes
System configuration TN-C			No
System configuration TN-C-S			No
System configuration TN-S			No
System configuration TT			No
System configuration other			Yes
Number of poles			1
Lightning impulse current (10/350 µs)		kA	12.5
Max. continuous voltage AC		V	280
Max. continuous voltage DC		V	0
Nominal voltage AC		V	280
Nominal voltage DC		V	0
Max. PV-voltage		V	0
Voltage protection level		kV	1.5
Voltage protection level L-N		kV	0
Voltage protection level L-PE		kV	1.5
Voltage protection level N-PE		kV	0
Voltage protection level (DC+ - DC-)		kV	0
Voltage protection level (DC+/DC- - PE)		kV	0
Follow current extinguishing capability		kA	0
Specific energy (W/R)		kJ/Ohm	39.1
Max. conductor cross section solid (solid, stranded)		mm ²	25
Max. conductor cross section flexible (fine-strand)		mm ²	35
Mounting method			DIN rail (top hat rail) 35 mm
Construction size			1 modular spacing
Remote signalling			No
Signalling at the device			Optic
Test class			Type 1 + 2
Exhausting			No
Integrated backup fuse			No
Energy-coordinated protection effect with regard to the terminal equipment			No
Degree of protection (IP)			IP20