

DATOVÝ LIST - EVG-2PHAS/12MODUL



Propojovací lišty, 2f, 12HP, 63A pro PLS. CLS. PKN., PFIM, PFHM, PFNM



Typ **EVG-2PHAS/12MODUL**
Catalog No. **215641**

Abbildung ähnlich

Dodavatelský program

Základní funkce			sběrnice
Základní funkční příslušenství			Přípojnice pro miniaturní jistič Přípojnice pro jističe reziduálního proudu Přípojnice pro kombinovaný jistič reziduálního proudu / výkonový jistič
Typ sběrnice			2fázový
Sortiment			EVG

Technická data podle ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Elektrotechnika, automatizační technika a technika řízení procesu / Nízkonapetová spínací technika / Komponenta pro nízkonapetovou spínací techniku / Phase busbar (ec1@ss10.0.1-27-37-13-06 [ACN992011])			
Number of phases			2
Number of poles			2
Suitable for number of devices			6
Pitch dimensions		mm	0
Cross section		mm ²	10
Length		mm	210
Number of modular spacings			12
Rated permanent current I _u		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I _q		kA	25
Max. rated operation voltage U _e		V	500
Rated short-time withstand current I _{cw}		kA	0
Suitable for devices with N-busbar			No
Suitable for devices with auxiliary switch			No