
DATOVÝ LIST - EVG-2PHAS/6MODUL



Propojovací lišty, 2f, 6HP, 63A pro PLS. CLS. PKN., PFIM, PFHM, PFNM

Typ **EVG-2PHAS/6MODUL**
Catalog No. **215642**

Powering Business Worldwide™

Abbildung ähnlich

Dodavatelský program

Základní funkce			sběrnice
Základní funkční příslušenství			Přípojnice pro miniaturní jistič Přípojnice pro jističe residuálního proudu Přípojnice pro kombinovaný jistič reziduálního proudu / výkonový jistič
Typ sběrnice			2fázový
Sortiment			EVG

Technická data podle ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)

Elektrotechnika, automatizacní technika a technika rízení procesu / Nízkonapetová spínací technika / Komponenta pro nízkonapetovou spínací techniku / Phase busbar (ecl@ss10.0.1-27-37-13-06 [ACN992011])

Number of phases			2
Number of poles			2
Suitable for number of devices			3
Pitch dimensions		mm	0
Cross section		mm^2	10
Length		mm	103
Number of modular spacings			6
Rated permanent current Iu		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current Iq		kA	25
Max. rated operation voltage Ue		V	500
Rated short-time withstand current Icw		kA	0
Suitable for devices with N-busbar			No
Suitable for devices with auxiliary switch			No

© 06/2021 by Eaton Industries GmbH