



Propojovací lišty, 4f, 12HP, 63A pro PLS. CLS. PKN., PFIM, PFHM, PFNM

**Typ** EVG-4PHAS/12MODUL  
**Catalog No.** 215643

Abbildung ähnlich

## Dodavatelský program

Základní funkce		sběrnice
Základní funkční příslušenství		Přípojnice pro miniaturní jistič Přípojnice pro jističe reziduálního proudu Přípojnice pro kombinovaný jistič reziduálního proudu / výkonový jistič
Typ sběrnice		4fázový
Sortiment		EVG

## Technická data podle ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Elektrotechnika, automatizační technika a technika řízení procesu / Nízkonapetová spínací technika / Komponenta pro nízkonapetovou spínací techniku / Phase busbar (ec1@ss10.0.1-27-37-13-06 [ACN992011])			
Number of phases			4
Number of poles			4
Suitable for number of devices			3
Pitch dimensions		mm	0
Cross section		mm <sup>2</sup>	10
Length		mm	210
Number of modular spacings			12
Rated permanent current I <sub>u</sub>		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I <sub>q</sub>		kA	25
Max. rated operation voltage U <sub>e</sub>		V	500
Rated short-time withstand current I <sub>cw</sub>		kA	0
Suitable for devices with N-busbar			Yes
Suitable for devices with auxiliary switch			No