



Propojovací lišty, 3f, 4+8HP, pro kombinovaný modul svodiče přepětí FI/LS s 4p-FI

Typ EVG-3PHAS/N/8MODUL/LS
Catalog No. 215660

Abbildung ähnlich

Dodavatelský program

Základní funkce		sběrnice
Základní funkční příslušenství		Přípojnice pro miniaturní jistič Přípojnice pro jističe reziduálního proudu Přípojnice pro kombinovaný jistič reziduálního proudu / výkonový jistič
Typ sběrnice		3fázový + pomocný kontakt
Sortiment		EVG

Technická data podle ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)		
Elektrotechnika, automatizační technika a technika řízení procesu / Nízkonapetová spínací technika / Komponenta pro nízkonapetovou spínací techniku / Phase busbar (ecI@ss10.0.1-27-37-13-06 [ACN992011])		
Number of phases		3
Number of poles		4
Suitable for number of devices		0
Pitch dimensions	mm	0
Cross section	mm ²	10
Length	mm	210
Number of modular spacings		8
Rated permanent current I _u	A	63
Type of electric connection		Fork
Insulated		Yes
Rated surge voltage	kV	4
Conditioned rated short-circuit current I _q	kA	25
Max. rated operation voltage U _e	V	500
Rated short-time withstand current I _{cw}	kA	0
Suitable for devices with N-busbar		No
Suitable for devices with auxiliary switch		No