



Řídicí spínač 13 S, 1 R, 16A, 230 V, 20kA

Typ Z-S/3S10
Catalog No. 248338

Abbildung ähnlich

Ověření návrhu podle ČSN EN 61439

Technické údaje pro ověření konstrukce			
Jmenovitý proud k údajům ztrátového výkonu	I_n	A	20

Technická data podle ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Main switch for distribution board (EC001545)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Modulární radový vestavený přístroj pro rozbovací proudových okruhu / Vestavený vypínač pro rozvody (ecl@ss10.0.1-27-14-23-01 [AFZ813014])			
Switching function			Control switch
Number of contacts as normally open contact			3
Number of contacts as normally closed contact			1
Number of contacts as change-over contact			0
Number of poles			0
Rated current		A	16
Rated voltage		V	230
Min. rated voltage		V	0
Rated switching capacity		kA	20
Short-circuit breaking capacity (Icw)		kA	10
Voltage type			AC
Forced segregation (according to DIN VDE 0113)			No
With signal lamp			No
Colour calotte			Other
Lamp type			Other
Lamp socket			Other
Max. lamp power		W	0
Width in number of modular spacings			1
Built-in depth		mm	80
Degree of protection (IP)			IP40