



Vypínač p22 W, 16A, 230 V, 20kA

Typ Z-S/2WM
Catalog No. 248346

Ověření návrhu podle ČSN EN 61439

Technické údaje pro ověření konstrukce			
Jmenovitý proud k údajům ztrátového výkonu	I_n	A	20

Technická data podle ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Main switch for distribution board (EC001545)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Modulární radový vestavený přístroj pro rozbočovací proudových okruhu / Vestavený vypínač pro rozvody (ecl@ss10.0.1-27-14-23-01 [AFZ813014])			
Switching function			Two-way switch
Number of contacts as normally open contact			0
Number of contacts as normally closed contact			0
Number of contacts as change-over contact			2
Number of poles			0
Rated current		A	16
Rated voltage		V	230
Min. rated voltage		V	0
Rated switching capacity		kA	20
Short-circuit breaking capacity (I _{cw})		kA	10
Voltage type			AC
Forced segregation (according to DIN VDE 0113)			No
With signal lamp			No
Colour calotte			Other
Lamp type			Other
Lamp socket			Other
Max. lamp power		W	0
Width in number of modular spacings			2
Built-in depth		mm	80
Degree of protection (IP)			IP40