



Spínače s LED, 230AC/DC, 1S, 16A, oranžový, 1HP

Typ Z-SWL230/S
Catalog No. 292300

Ověření návrhu podle ČSN EN 61439

Technické údaje pro ověření konstrukce			
Jmenovitý proud k údajům ztrátového výkonu	I_n	A	16
Ztrátový výkon na jeden pól, v závislosti na proudu	P_{vid}	W	2
Ztrátový výkon přístroje, v závislosti na proudu	P_{vid}	W	2

Technická data podle ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Main switch for distribution board (EC001545)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Modulární radový vestavený přístroj pro rozbočovací proudových okruhu / Vestavený vypínač pro rozvody (ec1@ss10.0.1-27-14-23-01 [AFZ813014])			
Switching function			Off switch
Number of contacts as normally open contact			1
Number of contacts as normally closed contact			0
Number of contacts as change-over contact			0
Number of poles			0
Rated current		A	16
Rated voltage		V	250
Min. rated voltage		V	0
Rated switching capacity		kA	0
Short-circuit breaking capacity (I _{cw})		kA	0
Voltage type			AC
Forced segregation (according to DIN VDE 0113)			No
With signal lamp			Yes
Colour calotte			Other
Lamp type			LED
Lamp socket			Other
Max. lamp power		W	0
Width in number of modular spacings			1
Built-in depth		mm	80
Degree of protection (IP)			IP40