



RF Spínací aktor 10A RLC / 230V AC s BIN vstupem

Typ CSAU-01/01-10I
Catalog No. 172938
Alternate Catalog No. CSAU-01/01-10I

Dodavatelský program

Typ produktu		Ovládání
Typ montáže		Zapuštěná montáž
Napájení		Síťové napájení
Aktivační funkce		Spínání

Technická data podle ETIM 7.0

Installation bus systems (EG000032) / Switch actuator for bus system (EC001097)		
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Sbernicový systém / Sbernicový systém - aktor (ecl@ss10.0.1-27-14-31-25 [AKE293014])		
Bus system KNX		No
Bus system KNX radio		No
Bus system radio frequent		Yes
Bus system LON		No
Bus system Powernet		No
Other bus systems		xComfort
Radio frequent bidirectional		Yes
Mounting method		Flush mounted (plaster)
Width in number of modular spacings		3
Local operation/hand operation		Yes
With LED indication		Yes
Number of binary inputs		1
Max. switching power	W	2300
Output power	W	2300
Suitable for C-load		Yes
Max. number of switching contacts		1
Max. switching current	A	10
Rated current	A	10
Rated operating voltage	V	230 - 230
Different phases connectable		No
Bus connection included		Yes
Bus module detachable		No
Min. depth of built-in installation box	mm	18
Modular expandability		No
Degree of protection (IP)		IP20