



RF Spínací aktor 10A RLC / 230V AC s BIN vstupem a měřičem spotřeby

Typ CSAU-01/01-10IE
Catalog No. 172939
Alternate Catalog No. CSAU-01/01-10IE

Dodavatelský program

Typ produktu		Ovládání
Typ montáže		Zapuštěná montáž
Napájení		Síťové napájení
Aktivační funkce		Spínání

Technická data podle ETIM 7.0

Installation bus systems (EG000032) / Switch actuator for bus system (EC001097)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Sbernicový systém / Sbernicový systém - aktor (ecl@ss10.0.1-27-14-31-25 [AKE293014])			
Bus system KNX			No
Bus system KNX radio			No
Bus system radio frequent			Yes
Bus system LON			No
Bus system Powernet			No
Other bus systems			xComfort
Radio frequent bidirectional			Yes
Mounting method			Flush mounted (plaster)
Width in number of modular spacings			3
Local operation/hand operation			Yes
With LED indication			Yes
Number of binary inputs			1
Max. switching power		W	2300
Output power		W	2300
Suitable for C-load			Yes
Max. number of switching contacts			1
Max. switching current		A	10
Rated current		A	10
Rated operating voltage		V	230 - 230
Different phases connectable			No
Bus connection included			Yes
Bus module detachable			No
Min. depth of built-in installation box		mm	18
Modular expandability			No
Degree of protection (IP)			IP20