



Propojovací lišty, 4f, 8HP, 63A pro PLS. CLS. PKN., PFIM, PFHM, PFNM



Typ EVG-4PHAS/8MODUL
Catalog No. 215644

Abbildung ähnlich

Dodavatelský program

Základní funkce		sběrnice
Základní funkční příslušenství		Připojnice pro miniaturní jistič Připojnice pro jističe reziduálního proudu Připojnice pro kombinovaný jistič reziduálního proudu / výkonový jistič
Typ sběrnice		4fázový
Sortiment		EVG

Technická data podle ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Elektrotechnika, automatizační technika a technika řízení procesu / Nízkonapetová spínací technika / Komponenta pro nízkonapetovou spínací techniku / Phase busbar (ecI@ss10.0.1-27-37-13-06 [ACN992011])			
Number of phases			4
Number of poles			4
Suitable for number of devices			2
Pitch dimensions		mm	0
Cross section		mm ²	10
Length		mm	142
Number of modular spacings			8
Rated permanent current I _u		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I _q		kA	25
Max. rated operation voltage U _e		V	500
Rated short-time withstand current I _{cw}		kA	0
Suitable for devices with N-busbar			Yes
Suitable for devices with auxiliary switch			No