



**Pomocný kontakt, pro PFIM, PFHM-4p, dRCM, PFR, 1S+1R, 0.5HP**

**Typ** Z-HK  
**Catalog No.** 248432

**Dodavatelský program**

Základní funkce		příslušenství pro proudový chránič
Základní funkční příslušenství		Pomocné kontakty
Použití		Spínací přístroje pro průmyslové použití a účelové stavby
Sortiment		Příslušenství
Side mounting		for fitting on left to: FI
Značka zapojení		

**Technická data**

**Ověření návrhu podle ČSN EN 61439**

Technické údaje pro ověření konstrukce		
Provozní teplota okolí min.	°C	-5
Provozní teplota okolí max.	°C	40

**Technická data podle ETIM 7.0**

Devices for distribution board-/surface mounting (EG000062) / Auxiliary device for distribution board devices (EC001286)		
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Komponenta ochranného snímače / Pomocný kontakt, signalizační kontakt (ecl@ss10.0.1-27-14-35-02 [AKE327013])		
Device fitting		Earth leakage switch
Additional equipment		Auxiliary switch
Attached at delivery		No
Assembly width (TE)		0.5
Number of contacts as normally open contact		1
Number of contacts as normally closed contact		1
Number of contacts as change-over contact		0
Number of fault-signal switches		0
Rated switch current	A	3
Rated voltage	V	230
Voltage type for actuating		AC
With auto test for earth leakage function		No
Suitable for max. number of poles main contact unit (total)		2
Suitable for max. current main contact unit	A	8

