



**Pomocný kontakt, pro PLS, PLZ, PKNM, ZP-A40, ZP-ASA, Z-MS, 2W, 0.5HP**

**Typ ZP-NHK**  
**Catalog No. 248437**

**Dodavatelský program**

Základní funkce		příslušenství pro proudový chránič s nadproudovou ochranou příslušenství pro instalační jistič
Základní funkční příslušenství		Kontakty vypínacího signálu
Použití		Spínací přístroje pro průmyslové použití a účelové stavby
Sortiment		Příslušenství
Side mounting		for fitting on left to: LS, FI/LS
Značka zapojení		

**Technická data**

**Ověření návrhu podle ČSN EN 61439**

Technické údaje pro ověření konstrukce			
Provozní teplota okolí min.		°C	-5
Provozní teplota okolí max.		°C	40

**Technická data podle ETIM 7.0**

Devices for distribution board-/surface mounting (EG000062) / Auxiliary device for distribution board devices (EC001286)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Komponenta ochranného snímace / Pomocný kontakt, signalizační kontakt (ec@ss10.0.1-27-14-35-02 [AKE327013])			
Device fitting			Universal
Additional equipment			Signalling switch
Attached at delivery			No
Assembly width (TE)			0.5
Number of contacts as normally open contact			0
Number of contacts as normally closed contact			0
Number of contacts as change-over contact			2
Number of fault-signal switches			0
Rated switch current		A	4
Rated voltage		V	250
Voltage type for actuating			AC
With auto test for earth leakage function			No
Suitable for max. number of poles main contact unit (total)			2
Suitable for max. current main contact unit		A	4

