

Produktdatablad

Artikel nr.	805319	Antal salgsheder	1 Pack
Farve	transparent	Salgshed EAN	4005546810539
Emballageenhed	pakke med 25 stk	Emballagevægt (brutto)	2962 G
Basis EAN	4005546810539	Oprindelsesland	DE



Logoer og udmærkelser



Produkt beskrivelse

- Stabilt, V-formet navneskilt
- Med udskiftelige blanke indstik, der kan læses fra begge sider
- Mål indstik: 105/210 x 297 mm

Produkt detaljer

Udvendig brede (mm)	297
Udvendig højde (mm)	92
Udvendig dybde/længde	115 mm
Orienteringsformat	tvær format
Brand	DURABLE

805319_PDS_DURABLE_da_DK.pdf | 2023-10-15 03:40

1/2

DURABLE Hunke & Jochheim GmbH & Co. KG
Postfach 1753 · 58634 Iserlohn
Westfalenstraße 77 – 79 · 58636 Iserlohn · Germany
Phone (0 23 71) 662 - 0 · Fax (0 23 71) 662 - 221
Mail durable@ durable.de | durable.de

The statements contained herein are for informational purposes only and are true and accurate to the best of our scientific and technical knowledge. This information does not constitute a guarantee or warranty, express or implied, nor does it establish a legally valid contractual relationship. It is the customer's responsibility to determine the suitability of this product for the customer's intended use. DURABLE does not assume any liability for the customer's use of this product or the information contained herein.



Indstiksarkets bredde (mm)	297
Indstiksarkets højde (mm)	105
Med neutrale etiketter	Ja
Vindue med udskiftelig etiket	Ja