



## DBY-23510 DBY510

Uhindret rækkevidde	100 m
LED-indikatoren ved tryk	Ja
Inklusiv batteri	Ja
Monteringsmetode	
Vægmonteret	Ja
Batteritype	CR2032
Trådløs	Ja
Radiofrekvens	433 MHz
Kompatibel	



: x x (cm): 16.5 x 9.6 x 3 | : 8711658450063  
(kg): 0.0498 | (kg): 0.0313

: x x (cm): 22.5 x 24.5 x 25 | : 8711658449999  
(kg): 1.4996

:: 24 | : 2400 | x : 4 x 25 | / / : 34800 / 69600 / 76560