

DBY-23412 B412

Uhindret rækkevidde	100 m
Antal melodier	16
Strømforsyning	
Lydstyrkejustering	
Nem isættelse	Ja
Decibelklassificering	80 dB
Strømforsyning dørklokke	
Strømsluktype	C - CEE 7/16 (flat plug)
Radiofrekvens	433,92 MHz



: x x (cm): 15 x 9.5 x 8.8 | : 8711658450476
(kg): 0.201 | (kg): 0.147

: x x (cm): 39.5 x 29 x 44.5 | : 8711658450544
(kg): 6.328

:: 24 | : 216 | x : 1 x 9 | / / : 13183 / 27308 / 30603

