

KERN EMB 600-2

KERN

Entry level laboratory balance with tremendous weighing performance



Display backlight	no
Display screen size	58×18 mm
Display digit height	15 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	170×244×39 mm
Dimensions weighing surface (Ø)	105 mm
Dimensions weighing surface	105 mm
Material housing	plastic
Material weighing plate	plastic
Material display housing	plastic

Functions

Underfloor weighing	Hook (included in delivery)
IP protection - complete device	-
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Number of keys for operation	2

Power Supply

Supplied power supply	Battery
Power supply type	Power adapter
	EURO
Plug-in power supply / adapter for countries - optional	UK US CH
Input voltage device / power [Max]	9 V, 300 mA
Power socket for mains adapter	Hollow plug, inside minus, Ø inside 2,1 mm, Ø outside 5,5 mm, long 12 mm
Battery / accumulator type	Alkali(-Manganese)
Battery	9 V block
Battery connection	Pad + Spring
Battery operating time	25 h
Battery voltage	9 V
Battery - Number of cells	1
Battery - Individual weight	45,5 g
Battery - Total weight	45,5 g
Rechargeable battery	KS-A01
Rechargeable battery operating time - backlight off	50 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional
Battery/Accu connected	not connected, enclosed

Category

Brand	KERN
Product category	Laboratory balance
Product group	School balance
Product family	EMB

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	600 g
Readability [d]	0,01 g
Reproducibility	0,01 g
Linearity	± 0,03 g
Resolution	60.000
Tare range	600 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	500 g (F2)
Possible calibration points	500 g
Stabilization time	2,5 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,03 g
Construction type of the scale	Single-range balance
Units	g dwt ozt oz
Maximum creep (15 minutes)	100 mg
Maximum creep (30 minutes)	200 mg
Default unit	g

Display

Display type	LCD
--------------	-----

KERN EMB 600-2



Entry level laboratory balance with tremendous weighing performance

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	210×265×90 mm
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	0,70 kg
Shipping weight	1 kg

Product information

GTIN/EAN number	4045761076556
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

