



Anbaumaße, mm

Motor Typ	A	B	C	H	K	D	E	F	G	AB	AC	AD	BB	LD	KK	HD	L
KAE1A56	90	71	36	56	6	9	20	3	7,2	108	120	101	90	55	M20 x 1,5	157	195
KAE1A63	100	80	40	63	7	11	23	4	8,5	120	128	109	105	63,5	M20 x 1,5	172	213
KAE1A71	112	90	45	71	7	14	30	5	11	132	145	117	105	69,5	M20 x 1,5	188	255
KAE1A80	125	100	50	80	10	19	40	6	15,5	158	158	136	125	86	M20 x 1,5	216	285
KAE1A90S	140	100	56	90	10	24	50	8	20	175	178	145	125	85	M20 x 1,5	235	306
KAE1A90L	140	125	56	90	10	24	50	8	20	175	178	145	150	85	M20 x 1,5	235	330
KAE1A100L	160	140	63	100	12	28	60	8	24	196	203	155	170	84	M20 x 1,5	255	372
KAE1A112	190	140	70	112	12	28	60	8	24	220	227	173	180	92	M32 x 1,5	285	395
KAE1A132S	216	140	89	132	12	38	80	10	33	256	266	193	180	105	M32 x 1,5	325	462
KAE1A132M	216	178	89	132	12	38	80	10	33	256	266	193	220	105	M32 x 1,5	325	500

2 polig	4 polig	Motor Typ
GM 63/2 0,25kW	GM 63/4	KAE 1A 63
GM 71/2 0,37kW/0,55kW	GM 71/4 0,25kW/0,37kW	KAE 1A 71
GM 80/2 0,75kW/1,1kW	GM 80/4 0,55kW/0,75kW	KAE 1A 80
GM 90/2 1,5kW	GM 90/4 1,1kW	KAE 1A 90 S
GM 90/2 2,2kW	GM 90/4 1,5kW	KAE 1A 90 L
	GM 100/4 2,2kW	KAE 1A 100 L

Titel:	Maßblatt
Type:	IE1 - B3