

Datenblatt / Data Sheet

T5.5K Slide Base Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70112252	T5.5*22mm	Red	12V	T5.5K	17±2mA	620-630	0.8 lm	30K(h)	60°
70112256	T5.5*22mm	Red	24-28V	T5.5K	16±2mA	620-630	0.8 lm	30K(h)	60°
70112266	T5.5*22mm	Green	12V	T5.5K	16±2mA	515-525	2 lm	30K(h)	60°
70112270	T5.5*22mm	Green	24-28V	T5.5K	17±2mA	515-525	2.1 lm	30K(h)	60°
70112280	T5.5*22mm	Blue	12V	T5.5K	17±2mA	465-475	0.3 lm	30K(h)	60°
70112284	T5.5*22mm	Blue	24-28V	T5.5K	16±2mA	465-475	0.3 lm	30K(h)	60°
70112294	T5.5*22mm	Amber	12V	T5.5K	17±2mA	590-600	0.4 lm	30K(h)	60°
70112298	T5.5*22mm	Amber	24-28V	T5.5K	16±2mA	590-600	0.4 lm	30K(h)	60°
70112306	T5.5*22mm	White	6V	T5.5K	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112308	T5.5*22mm	White	12V	T5.5K	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112312	T5.5*22mm	White	24-28V	T5.5K	17±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112314	T5.5*22mm	White	36V	T5.5K	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112316	T5.5*22mm	White	48V	T5.5K	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112318	T5.5*22mm	White	60V	T5.5K	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°