

Datenblatt / Data Sheet

T5.5 Slide Base Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70112322	T5.5*28mm	Red	12V	T5.5	17±2mA	620-630	0.8 lm	30K(h)	60°
70112326	T5.5*28mm	Red	24-28V	T5.5	16±2mA	620-630	0.8 lm	30K(h)	60°
70112336	T5.5*28mm	Green	12V	T5.5	16±2mA	515-525	2 lm	30K(h)	60°
70112340	T5.5*28mm	Green	24-28V	T5.5	17±2mA	515-525	2.1 lm	30K(h)	60°
70112350	T5.5*28mm	Blue	12V	T5.5	17±2mA	465-475	0.3 lm	30K(h)	60°
70112354	T5.5*28mm	Blue	24-28V	T5.5	16±2mA	465-475	0.3 lm	30K(h)	60°
70112364	T5.5*28mm	Amber	12V	T5.5	17±2mA	590-600	0.4 lm	30K(h)	60°
70112368	T5.5*28mm	Amber	24-28V	T5.5	16±2mA	590-600	0.4 lm	30K(h)	60°
70112376	T5.5*28mm	White	6V	T5.5	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112378	T5.5*28mm	White	12V	T5.5	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112382	T5.5*28mm	White	24-28V	T5.5	17±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112384	T5.5*28mm	White	36V	T5.5	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112386	T5.5*28mm	White	48V	T5.5	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112388	T5.5*28mm	White	60V	T5.5	16±2mA	(K)5000-6000	2.1 lm	30K(h)	60°