

Datenblatt / Data Sheet

T5.8MG (S4s) Single Midget Grooved Base Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70112392	T5.8*16mm	Red	12V	S4s	20±2mA	620-630	0.7 lm	30K(h)	95°
70112396	T5.8*16mm	Red	24-28V	S4s	20±2mA	620-630	0.7 lm	30K(h)	95°
70112402	T5.8*16mm	Red	60V	S4s	14±2mA	620-630	0.4lm	30K(h)	95°
70112406	T5.8*16mm	Green	12V	S4s	19±2mA	515-525	1.3lm	30K(h)	95°
70112410	T5.8*16mm	Green	24-28V	S4s	19±2mA	515-525	1.3 lm	30K(h)	95°
70112416	T5.8*16mm	Green	60V	S4s	13±2mA	515-525	0.8 lm	30K(h)	95°
70112420	T5.8*16mm	Blue	12V	S4s	19±2mA	465-475	0.5 lm	30K(h)	95°
70112424	T5.8*16mm	Blue	24-28V	S4s	19±2mA	465-475	0.5 lm	30K(h)	95°
70112430	T5.8*16mm	Blue	60V	S4s	13±2mA	465-475	0.3 lm	30K(h)	95°
70112434	T5.8*16mm	Amber	12V	S4s	21±2mA	585-595	0.3 lm	30K(h)	95°
70112438	T5.8*16mm	Amber	24-28V	S4s	20±2mA	585-595	0.3 lm	30K(h)	95°
70112444	T5.8*16mm	Amber	60V	S4s	13±2mA	585-595	0.2 lm	30K(h)	95°
70112446	T5.8*16mm	White	6V	S4s	19±2mA	(K)5000-6000	1.2 lm	30K(h)	95°
70112448	T5.8*16mm	White	12V	S4s	19±2mA	(K)5000-6000	1.2 lm	30K(h)	95°
70112452	T5.8*16mm	White	24-28V	S4s	19±2mA	(K)5000-6000	1.1 lm	30K(h)	95°
70112454	T5.8*16mm	White	36V	S4s	14±2mA	(K)5000-6000	1.1 lm	30K(h)	95°
70112456	T5.8*16mm	White	48V	S4s	14±2mA	(K)5000-6000	1.1 lm	30K(h)	95°
70112458	T5.8*16mm	White	60V	S4s	13±2mA	(K)5000-6000	1.0 lm	30K(h)	95°