

## Datenblatt / Data Sheet

### T6.8G Slide Base Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70112762	T6.8*43mm	Red	12V	T6.8G	18mA	620-630	0.8 lm	30K(h)	60°
70112766	T6.8*43mm	Red	24-28V	T6.8G	15mA	620-630	0.7 lm	30K(h)	60°
70112768	T6.8*43mm	Red	30V	T6.8G	14mA	620-630	0.6 lm	30K(h)	60°
70112774	T6.8*43mm	Red	60V	T6.8G	10mA	620-630	0.4 lm	30K(h)	60°
70112776	T6.8*43mm	Red	70V	T6.8G	9mA	620-630	0.4 lm	30K(h)	60°
70112780	T6.8*43mm	Green	12V	T6.8G	17mA	515-525	2 lm	30K(h)	60°
70112784	T6.8*43mm	Green	24-28V	T6.8G	14mA	515-525	1.7 lm	30K(h)	60°
70112786	T6.8*43mm	Green	30V	T6.8G	14mA	515-525	1.7 lm	30K(h)	60°
70112792	T6.8*43mm	Green	60V	T6.8G	10mA	515-525	1.2 lm	30K(h)	60°
70112794	T6.8*43mm	Green	70V	T6.8G	9mA	515-525	1.1 lm	30K(h)	60°
70112798	T6.8*43mm	Blue	12V	T6.8G	17mA	465-475	0.5 lm	30K(h)	60°
70112802	T6.8*43mm	Blue	24-28V	T6.8G	14mA	465-475	0.4 lm	30K(h)	60°
70112804	T6.8*43mm	Blue	30V	T6.8G	14mA	465-475	0.4 lm	30K(h)	60°
70112810	T6.8*43mm	Blue	60V	T6.8G	10mA	465-475	0.3 lm	30K(h)	60°
70112812	T6.8*43mm	Blue	70V	T6.8G	9mA	465-475	0.25 lm	30K(h)	60°
70112816	T6.8*43mm	Amber	12V	T6.8G	18mA	585-595	0.6 lm	30K(h)	60°
70112820	T6.8*43mm	Amber	24-28V	T6.8G	14mA	585-595	0.5 lm	30K(h)	60°
70112822	T6.8*43mm	Amber	30V	T6.8G	14mA	585-595	0.5 lm	30K(h)	60°
70112828	T6.8*43mm	Amber	60V	T6.8G	10mA	585-595	0.35 lm	30K(h)	60°
70112830	T6.8*43mm	Amber	70V	T6.8G	9mA	585-595	0.3 lm	30K(h)	60°
70112834	T6.8*43mm	White	12V	T6.8G	17mA	(K)5000-6000	2.1 lm	30K(h)	60°
70112838	T6.8*43mm	White	24-28V	T6.8G	14mA	(K)5000-6000	1.7 lm	30K(h)	60°
70112840	T6.8*43mm	White	30V	T6.8G	14mA	(K)5000-6000	1.7 lm	30K(h)	60°
70112846	T6.8*43mm	White	60V	T6.8G	10mA	(K)5000-6000	1.4 lm	30K(h)	60°
70112848	T6.8*43mm	White	70V	T6.8G	9mA	(K)5000-6000	1.3 lm	30K(h)	60°