

## Datenblatt / Data Sheet

### T7 BA7S Single Dome Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70112850	T7*20mm	Red	6V	BA7S	16±2mA	620-630	0.6 lm	30K (h)	95°
70112852	T7*20mm	Red	12V	BA7S	16±2mA	620-630	0.6 lm	30K (h)	95°
70112856	T7*20mm	Red	24-28V	BA7S	17±2mA	620-630	0.6 lm	30K (h)	95°
70112864	T7*20mm	Green	6V	BA7S	15±2mA	515-525	1.0 lm	30K (h)	95°
70112866	T7*20mm	Green	12V	BA7S	15±2mA	515-525	1.0 lm	30K (h)	95°
70112870	T7*20mm	Green	24-28V	BA7S	16±2mA	515-525	1.1 lm	30K (h)	95°
70112878	T7*20mm	Blue	6V	BA7S	16±2mA	465-475	0.4 lm	30K (h)	95°
70112880	T7*20mm	Blue	12V	BA7S	16±2mA	465-475	0.4 lm	30K (h)	95°
70112884	T7*20mm	Blue	24-28V	BA7S	16±2mA	465-475	0.4 lm	30K (h)	95°
70112892	T7*20mm	Amber	6V	BA7S	16±2mA	585-595	0.4 lm	30K (h)	95°
70112894	T7*20mm	Amber	12V	BA7S	16±2mA	585-595	0.4 lm	30K (h)	95°
70112898	T7*20mm	Amber	24-28V	BA7S	17±2mA	585-595	0.4 lm	30K (h)	95°
70112906	T7*20mm	White	6V	BA7S	17±2mA	(K)5000-6000	1.3 lm	30K (h)	95°
70112908	T7*20mm	White	12V	BA7S	17±2mA	(K)5000-6000	1.3 lm	30K (h)	95°
70112912	T7*20mm	White	24-28V	BA7S	17±2mA	(K)5000-6000	1.3 lm	30K (h)	95°
70112914	T7*20mm	White	36V	BA7S	14±2mA	(K)5000-6000	1.1 lm	30K (h)	95°
70112916	T7*20mm	White	48V	BA7S	14±2mA	(K)5000-6000	1.1 lm	30K (h)	95°
70112918	T7*20mm	White	60V	BA7S	13±2mA	(K)5000-6000	1.0 lm	30K (h)	95°