

Datenblatt / Data Sheet

T10 Wedge Base Lamp (Dome)



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70112990	T10*28mm	Red	6V	W2.1*9.5d	17±2mA	620-630	0.7 lm	30K (h)	45°
70112992	T10*28mm	Red	12V	W2.1*9.5d	17±2mA	620-630	0.7 lm	30K (h)	45°
70112996	T10*28mm	Red	24-28V	W2.1*9.5d	18±2mA	620-630	0.75 lm	30K (h)	45°
70112998	T10*28mm	Green	6V	W2.1*9.5d	16±2mA	515-525	2.0 lm	30K (h)	45°
70113000	T10*28mm	Green	12V	W2.1*9.5d	16±2mA	515-525	2.0 lm	30K (h)	45°
70113004	T10*28mm	Green	24-28V	W2.1*9.5d	17 ±2mA	515-525	2.0 lm	30K (h)	45°
70113006	T10*28mm	Blue	6V	W2.1*9.5d	17±2mA	465-475	0.9 lm	30K (h)	45°
70113008	T10*28mm	Blue	12V	W2.1*9.5d	17±2mA	465-475	0.9 lm	30K (h)	45°
70113012	T10*28mm	Blue	24-28V	W2.1*9.5d	18±2mA	465-475	0.9 lm	30K (h)	45°
70113014	T10*28mm	Amber	6V	W2.1*9.5d	17±2mA	590-600	0.6 lm	30K (h)	45°
70113016	T10*28mm	Amber	12V	W2.1*9.5d	17±2mA	590-600	0.6 lm	30K (h)	45°
70113020	T10*28mm	Amber	24-28V	W2.1*9.5d	18 ±2mA	590-600	0.65 lm	30K (h)	45°
70113022	T10*28mm	White	6V	W2.1*9.5d	16±2mA	(K)5000-6000	2.9 lm	30K (h)	45°
70113024	T10*28mm	White	12V	W2.1*9.5d	16 ±2mA	(K)5000-6000	2.9 lm	30K (h)	45°
70113028	T10*28mm	White	24-28V	W2.1*9.5d	17±2mA	(K)5000-6000	2.9 lm	30K (h)	45°