

## Datenblatt / Data Sheet

### T10 E-10 Multi 2Chips Flat Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70113122	T10*23mm	Red	12V	E-10	23±2mA	620-630	1.2 lm	30K(h)	120°
70113126	T10*23mm	Red	24-28V	E-10	23±2mA	620-630	1.2 lm	30K(h)	120°
70113132	T10 23mm	Red	60V	E-10	12±2mA	620-630	0.8 lm	30K(h)	120°
70113136	T10 23mm	Red	220V AC	E-10	3±2mA	620-630	0.2 lm	30K(h)	120°
70113140	T10 23mm	Green	12V	E-10	21±2mA	515-525	2.3 lm	30K(h)	120°
70113144	T10 23mm	Green	24-28V	E-10	21±2mA	515-525	2.3 lm	30K(h)	120°
70113150	T10*23mm	Green	60V	E-10	11±2mA	515-525	1.2 lm	30K(h)	120°
70113154	T10*23mm	Green	220V AC	E-10	3±2mA	515-525	0.6 lm	30K(h)	120°
70113158	T10*23mm	Blue	12V	E-10	20±2mA	465-475	0.6 lm	30K(h)	120°
70113162	T10*23mm	Blue	24-28V	E-10	20±2mA	465-475	0.6 lm	30K(h)	120°
70113168	T10 23mm	Blue	60V	E-10	11±2mA	465-475	0.3 lm	30K(h)	120°
70113172	T10 23mm	Blue	220V AC	E-10	3±2mA	465-475	0.1 lm	30K(h)	120°
70113176	T10 23mm	Amber	12V	E-10	23±2mA	585-595	1.1 lm	30K(h)	120°
70113180	T10 23mm	Amber	24-28V	E-10	23±2mA	585-595	1.1 lm	30K(h)	120°
70113186	T10*23mm	Amber	60V	E-10	14±2mA	585-595	0.7 lm	30K(h)	120°
70113190	T10*23mm	Amber	220V AC	E-10	3±2mA	585-595	0.3 lm	30K(h)	120°
70113192	T10 23mm	White	6V	E-10	21±2mA	(K)5000-6000	2.2 lm	30K(h)	120°
70113194	T10*23mm	White	12V	E-10	21±2mA	(K)5000-6000	2.2 lm	30K(h)	120°
70113198	T10*23mm	White	24-28V	E-10	21±2mA	(K)5000-6000	2.2 lm	30K(h)	120°
70113200	T10 23mm	White	36V	E-10	18±2mA	(K)5000-6000	2.0 lm	30K(h)	120°
70113202	T10*23mm	White	48V	E-10	14±2mA	(K)5000-6000	1.7 lm	30K(h)	120°
70113204	T10 23mm	White	60V	E-10	11±2mA	(K)5000-6000	1.3 lm	30K(h)	120°
70113208	T10 23mm	White	220V AC	E-10	3±2mA	(K)5000-6000	0.6 lm	30K(h)	120°