

Datenblatt / Data Sheet

T10 BA9S Multi 4Chips Flat Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70113212	T10*23mm	Red	12V	BA9S	24±2mA	620-630	2.4 lm	30K(h)	120°
70113216	T10*23mm	Red	24-28V	BA9S	24±2mA	620-630	2.4 lm	30K(h)	120°
70113222	T10*23mm	Red	60V	BA9S	13±2mA	620-630	1.4 lm	30K(h)	120°
70113226	T10*23mm	Red	220V AC	BA9S	4±2mA	620-630	0.4 lm	30K(h)	120°
70113230	T10*23mm	Green	12V	BA9S	18±2mA	515-525	3.6 lm	30K(h)	120°
70113234	T10*23mm	Green	24-28V	BA9S	18±2mA	515-525	3.6 lm	30K(h)	120°
70113240	T10*23mm	Green	60V	BA9S	11±2mA	515-525	1.6 lm	30K(h)	120°
70113244	T10*23mm	Green	220V AC	BA9S	3±2mA	515-525	0.7 lm	30K(h)	120°
70113248	T10*23mm	Blue	12V	BA9S	20±2mA	465-475	0.9 lm	30K(h)	120°
70113252	T10*23mm	Blue	24-28V	BA9S	20±2mA	465-475	0.9 lm	30K(h)	120°
70113258	T10*23mm	Blue	60V	BA9S	11±2mA	465-475	0.5 lm	30K(h)	120°
70113262	T10*23mm	Blue	220V AC	BA9S	3±2mA	465-475	0.2 lm	30K(h)	120°
70113266	T10*23mm	Amber	12V	BA9S	24±2mA	585-595	3.0 lm	30K(h)	120°
70113270	T10*23mm	Amber	24-28V	BA9S	24±2mA	585-595	3.0 lm	30K(h)	120°
70113276	T10*23mm	Amber	60V	BA9S	13±2mA	585-595	1.6 lm	30K(h)	120°
70113280	T10*23mm	Amber	220V AC	BA9S	4±2mA	585-595	0.6 lm	30K(h)	120°
70113282	T10*23mm	White	6V	BA9S	18±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113284	T10*23mm	White	12V	BA9S	18±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113288	T10*23mm	White	24-28V	BA9S	18±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113290	T10*23mm	White	36V	BA9S	16±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113292	T10*23mm	White	48V	BA9S	14±2mA	(K)5000-6000	3.5 lm	30K(h)	120°
70113294	T10*23mm	White	60V	BA9S	11±2mA	(K)5000-6000	2.8 lm	30K(h)	120°
70113298	T10*23mm	White	220V AC	BA9S	4±2mA	(K)5000-6000	1.2 lm	00K(h)	120°