

## Datenblatt / Data Sheet

### T10 E-10 Multi 4Chips Flat Lamp



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70113302	T10*23mm	Red	12V	E-10	24±2mA	620-630	2.4 lm	30K(h)	120°
70113306	T10*23mm	Red	24-28V	E-10	24±2mA	620-630	2.4 lm	30K(h)	120°
70113312	T10*23mm	Red	60V	E-10	13±2mA	620-630	1.4 lm	30K(h)	120°
70113316	T10*23mm	Red	220V AC	E-10	4±2mA	620-630	0.4 lm	30K(h)	120°
70113320	T10*23mm	Green	12V	E-10	18±2mA	515-525	3.6 lm	30K(h)	120°
70113324	T10*23mm	Green	24-28V	E-10	18±2mA	515-525	3.6 lm	30K(h)	120°
70113330	T10*23mm	Green	60V	E-10	11±2mA	515-525	1.6 lm	30K(h)	120°
70113334	T10*23mm	Green	220V AC	E-10	3±2mA	515-525	0.7 lm	30K(h)	120°
70113338	T10*23mm	Blue	12V	E-10	20±2mA	465-475	0.9 lm	30K(h)	120°
70113342	T10*23mm	Blue	24-28V	E-10	20±2mA	465-475	0.9 lm	30K(h)	120°
70113348	T10*23mm	Blue	60V	E-10	11±2mA	465-475	0.5 lm	30K(h)	120°
70113352	T10*23mm	Blue	220V AC	E-10	3±2mA	465-475	0.2 lm	30K(h)	120°
70113356	T10*23mm	Amber	12V	E-10	24±2mA	585-595	3.0 lm	30K(h)	120°
70113360	T10*23mm	Amber	24-28V	E-10	24±2mA	585-595	3.0 lm	30K(h)	120°
70113366	T10*23mm	Amber	60V	E-10	13±2mA	585-595	1.6 lm	30K(h)	120°
70113370	T10*23mm	Amber	220V AC	E-10	4±2mA	585-595	0.6 lm	30K(h)	120°
70113372	T10*23mm	White	6V	E-10	18±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113374	T10*23mm	White	12V	E-10	18±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113378	T10*23mm	White	24-28V	E-10	18±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113380	T10*23mm	White	36V	E-10	16±2mA	(K)5000-6000	3.8 lm	30K(h)	120°
70113382	T10*23mm	White	48V	E-10	14±2mA	(K)5000-6000	3.5 lm	30K(h)	120°
70113384	T10*23mm	White	60V	E-10	11±2mA	(K)5000-6000	2.8 lm	30K(h)	120°
70113388	T10*23mm	White	220V AC	E-10	4±2mA	(K)5000-6000	1.2 lm	30K(h)	120°