

Datenblatt / Data Sheet

LED – Lampe mit Brückengleichrichter

LED bulb with bridge rectifier



Technische Daten / technical data

<i>Bezeichnung / Description</i>	<i>Eigenschaften / Characteristics</i>					
<i>Artikelnummer / Item no.</i>	59102311	59102312	59102313	59102314	59102315	59102326
<i>Farbe / Color</i>	Rot Red	Gelb Yellow	Grün Green	Blau Blue	Weiß White	Warmweiß Warm white
<i>Spannung / Voltage</i>	230V AC/DC					
<i>Strom / Current</i>	4mA	4mA	3mA	3mA	3mA	3mA
<i>Lichtstrom / Luminous flux</i>	0.1lm	0.1lm	0.3lm	0.1lm	0.2lm	0.2lm
<i>Sockel / Socket</i>	E10					
<i>Material / Material</i>	Kunststoff klar / Plastic clear					
<i>Merkmal / Feature</i>	Superhell / Superbright					
<i>Abmessungen / Dimension</i>	Ø10 x 28 mm					

Abmaße / Dimensions

