



Leitfähige Scharnierdeckelbehälter mit leitfähiger Steckschaumeinlage von 6 mm.

Conductive hinged lid boxes with conductive foam insert of 6 mm.

Innenabmessungen <i>internal dimensions</i>	Tiefe Unterteil <i>bottom height</i>	Bestellnr. <i>order-no.</i>
36 x 36 x 11 mm	6 mm	<b>C-199 2223</b>
74 x 51 x 21 mm	14 mm	<b>C-186 203</b>
80 x 54 x 17 mm	12 mm	<b>C-186 074</b>
90 x 64 x 19 mm	13 mm	<b>C-199 2231</b>
108 x 83 x 13 mm	10 mm	<b>C-186 228</b>
180 x 103 x 30 mm	28 mm	<b>C-186 258</b>
228 x 125 x 20 mm	10 mm	<b>C-186 256</b>
228 x 125 x 30 mm	20 mm	<b>C-186 257</b>
253 x 152 x 38 mm	38 mm	<b>C-199 2237</b>

	Behälter box	Steckschaum foam
Material material	Polypropylen <i>polypropylene</i>	Polyurethan <i>polyurethane</i>
Widerstand resistance	ca. $10^4 \Omega$	ca. $10^3 - 10^4 \Omega$
Farbe color	schwarz / black	
Raumgewicht density	40 kg / m <sup>3</sup>	
Stauchhärte Compression load deflection	50 kPa (40%)	