



Anbaumaße, mm

| Motor Typ | A | B | C | H | K | D | E | F | G | AB | AC | AD | BB | LD | KK | HD | L |
|-----------|-----|-----|----|-----|----|----|----|----|------|-----|-----|-----|-----|------|-----------|-----|-----|
| KAE1A56 | 90 | 71 | 36 | 56 | 6 | 9 | 20 | 3 | 7,2 | 108 | 120 | 101 | 90 | 55 | M20 x 1,5 | 157 | 195 |
| KAE1A63 | 100 | 80 | 40 | 63 | 7 | 11 | 23 | 4 | 8,5 | 120 | 128 | 109 | 105 | 63,5 | M20 x 1,5 | 172 | 213 |
| KAE1A71 | 112 | 90 | 45 | 71 | 7 | 14 | 30 | 5 | 11 | 132 | 145 | 117 | 105 | 69,5 | M20 x 1,5 | 188 | 255 |
| KAE1A80 | 125 | 100 | 50 | 80 | 10 | 19 | 40 | 6 | 15,5 | 158 | 158 | 136 | 125 | 86 | M20 x 1,5 | 216 | 285 |
| KAE1A90S | 140 | 100 | 56 | 90 | 10 | 24 | 50 | 8 | 20 | 175 | 178 | 145 | 125 | 85 | M20 x 1,5 | 235 | 306 |
| KAE1A90L | 140 | 125 | 56 | 90 | 10 | 24 | 50 | 8 | 20 | 175 | 178 | 145 | 150 | 85 | M20 x 1,5 | 235 | 330 |
| KAE1A100L | 160 | 140 | 63 | 100 | 12 | 28 | 60 | 8 | 24 | 196 | 203 | 155 | 170 | 84 | M20 x 1,5 | 255 | 372 |
| KAE1A112 | 190 | 140 | 70 | 112 | 12 | 28 | 60 | 8 | 24 | 220 | 227 | 173 | 180 | 92 | M32 x 1,5 | 285 | 395 |
| KAE1A132S | 216 | 140 | 89 | 132 | 12 | 38 | 80 | 10 | 33 | 256 | 266 | 193 | 180 | 105 | M32 x 1,5 | 325 | 462 |
| KAE1A132M | 216 | 178 | 89 | 132 | 12 | 38 | 80 | 10 | 33 | 256 | 266 | 193 | 220 | 105 | M32 x 1,5 | 325 | 500 |

| 2 polig | 4 polig | Motor Typ |
|-----------------------|-----------------------|--------------|
| GM 63/2 0,25kW | GM 63/4 | KAE 1A 63 |
| GM 71/2 0,37kW/0,55kW | GM 71/4 0,25kW/0,37kW | KAE 1A 71 |
| GM 80/2 0,75kW/1,1kW | GM 80/4 0,55kW/0,75kW | KAE 1A 80 |
| GM 90/2 1,5kW | GM 90/4 1,1kW | KAE 1A 90 S |
| GM 90/2 2,2kW | GM 90/4 1,5kW | KAE 1A 90 L |
| | GM 100/4 2,2kW | KAE 1A 100 L |

| | |
|--------|----------|
| Titel: | Maßblatt |
| Type: | IE1 - B3 |