

Datenblatt / Data Sheet

LED Signallampe Snap-In 5mm

LED signal lamp snap-in 5mm



*Kabelfarben je nach Artikel variabel
 *Cable colors variable depending on item

Technische Daten / Technical data

Bezeichnung / Description	Eigenschaften / Characteristics				
CE Artikelnummer / CE item no.	405441	405443	405444	405445	405447
Artikelnummer Hersteller / Producer item no.	52050611	52050612	52050613	52050614	52050615
Farbe / Colour	rot / red	gelb / yellow	grün / green	blau / blue	weiß / white
Betriebsspannung / Operating voltage	5-6V DC				
Betriebsstrom / Operating current	14-20mA				
Durchmesser LED / LED diameter	5mm				
Einbaudurchmesser / Mounting diameter	6.5mm				
Anschlußart / Connection type	150mm Litze AWG26 / 150mm cable AWG26				
Polarität Kabel / Polarity cable	gelb/yellow: "minus" – 2. Ader/2 nd wire: "plus"				

CE Artikelnummer / CE item no.	405448	405449	405451	405452	405453
Artikelnummer Hersteller / Producer item no.	52051411	52051412	52051413	52051414	52051415
Farbe / Colour	rot / red	gelb / yellow	grün / green	blau / blue	weiß / white
Betriebsspannung / Operating voltage	12-14V DC				
Betriebsstrom / Operating current	12-16mA				
Durchmesser LED / LED diameter	5mm				
Einbaudurchmesser / Mounting diameter	6.5mm				
Anschlußart / Connection type	150mm Litze AWG26 / 150mm cable AWG26				
Polarität Kabel / Polarity cable	gelb/yellow: "minus" – 2. Ader/2 nd wire: "plus"				

CE Artikelnummer / CE item no.	405454	405455	405456	405457	405458
Artikelnummer Hersteller / Producer item no.	52052811	52052812	52052813	52052814	52052815
Farbe / Colour	rot / red	gelb / yellow	grün / green	blau / blue	weiß / white
Betriebsspannung / Operating voltage	24-28V DC				
Betriebsstrom / Operating current	12-16mA				
Durchmesser LED / LED diameter	5mm				
Einbaudurchmesser / Mounting diameter	6.5mm				
Anschlußart / Connection type	150mm Litze AWG26 / 150mm cable AWG26				
Polarität Kabel / Polarity cable	gelb/yellow: "minus" – 2. Ader/2 nd wire: "plus"				