



Maße	M 3	M 4	M 5	M 6	M 8	M 10	M 12	M 14
$d_{k \max}$	5,8	6,5	7,5	9,5	12,5	15	17	20
m_{\max}	2,4	3,2	4	5	6,5	8	10	11
r	2,9	3,25	3,75	4,75	6,25	7,5	8,5	10
$S_{\text{DIN/ISO}}$	5,5	7	8	10	13	17 / 16	19 / 18	22 / 21
t_{\min}	4,5	5,26	7,21	7,71	10,65	12,65	15,65	17,65
W_{\min}	2	2	2	2	2	2	3	4

Maße	M 16	M 18	M 20	M 22	M 24	M 27	M 30
$d_{k \max}$	23	26	28	33	34	39	44
m_{\max}	13	15	16	18	19	22	24
r	11,5	13	14	16,5	17	19,5	22
$S_{\text{DIN/ISO}}$	24	27	30	32 / 34	36	41	46
t_{\min}	20,58	24,58	25,58	28,58	30,5	35	39
W_{\min}	4	5	5	5	6	7	7