



Bemerkung:

Werkstoff: Messing, vernickelt  
 Längentoleranz: 0,10 mm

Sonderlängen: ab 1000 Stück



Art.-Nr.	SW	L	Zoll	C1/C2	G1/G2
6135-5	5.5	5		5/5	M3/M3
6135-6	5.5	6		6/6	M3/M3
6135-7	5.5	7		7/7	M3/M3
6135-8	5.5	8		8/8	M3/M3
6135-9	5.5	9		9/9	M3/M3
6135-10	5.5	10		10/10	M3/M3
6135-11	5.5	11		11/11	M3/M3
6135-12	5.5	12		12/12	M3/M3
6135-13	5.5	13		13/13	M3/M3
6135-14	5.5	14		14/14	M3/M3
6135-15	5.5	15		15/15	M3/M3
6135-16	5.5	16		8/8	M3/M3
6135-17	5.5	17		8/8	M3/M3
6135-18	5.5	18		8/8	M3/M3
6135-19	5.5	19		8/8	M3/M3
6135-20	5.5	20		10/10	M3/M3
6135-21	5.5	21		10/10	M3/M3
6135-22	5.5	22		10/10	M3/M3
6135-23	5.5	23		10/10	M3/M3
6135-24	5.5	24		10/10	M3/M3
6135-25	5.5	25		10/10	M3/M3
6135-26	5.5	26		10/10	M3/M3
6135-27	5.5	27		10/10	M3/M3
6135-28	5.5	28		10/10	M3/M3
6135-29	5.5	29		10/10	M3/M3
6135-30	5.5	30		10/10	M3/M3
6135-31	5.5	31		10/10	M3/M3

ab Lager	ab x Stück	*
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Ja		
Nein	1000	

