



Bemerkung:

Werkstoff: Messing, vernickelt

Längentoleranz: 0,10 mm

Sonderlängen: ab 1000 Stück

PG = Preisgruppe



Art.-Nr.	SW	L	Zoll	C/B	G1/G2	PG	ab Lager	ab x Stück	*
6035-5	5.5	5		2.5/8	M3/M3	89	Ja		
6035-05 B6	5.5	5		2.5/6	M3/M3	89	Ja		
6035-6	5.5	6		3/8	M3/M3	93	Ja		
6035-7	5.5	7		4/8	M3/M3	93	Ja		
6035-8	5.5	8		5/8	M3/M3	93	Ja		
6035-08 B6	5.5	8		5/6	M3/M3	93	Ja		
6035-9	5.5	9		5/8	M3/M3	96	Ja		
6035-10	5.5	10		5/8	M3/M3	96	Ja		
6035-10 B6	5.5	10		5/6	M3/M3	96	Ja		
6035-11	5.5	11		6/8	M3/M3	98	Ja		
6035-12	5.5	12		6/8	M3/M3	98	Ja		
6035-12 B6	5.5	12		6/6	M3/M3	98	Ja		
6035-13	5.5	13		8/8	M3/M3	105	Ja		
6035-14	5.5	14		8/8	M3/M3	105	Ja		
6035-15	5.5	15		10/8	M3/M3	105	Ja		
6035-15 B6	5.5	15		7/6	M3/M3	105	Ja		
6035-16	5.5	16		10/8	M3/M3	112	Ja		
6035-17	5.5	17		10/8	M3/M3	112	Ja		
6035-18	5.5	18		10/8	M3/M3	115	Ja		
6035-19	5.5	19		10/8	M3/M3	115	Ja		
6035-20	5.5	20		10/8	M3/M3	115	Ja		
6035-20 B6	5.5	20		7/6	M3/M3	115	Ja		
6035-21	5.5	21		10/8	M3/M3	120	Nein	1000	
6035-22	5.5	22		10/8	M3/M3	120	Ja		
6035-23	5.5	23		10/8	M3/M3	120	Nein	1000	
6035-24	5.5	24		10/8	M3/M3	120	Nein	1000	
6035-25	5.5	25		10/10	M3/M3	120	Ja		

6035-25 B6	5.5	25		7/6	M3/M3	120	Ja		
6035-30 B6	5.5	30		7/6	M3/M3	128	Ja		
6035-35 B6	5.5	35		7/6	M3/M3	136	Ja		
6035-40 B6	5.5	40		7/6	M3/M3	141	Ja		
6035-45 B6	5.5	45		7/6	M3/M3	146	Ja		
6035-50 B6	5.5	50		7/6	M3/M3	155	Ja		
6035-55 B6	5.5	55		7/6	M3/M3	158	Ja		
6035-60 B6	5.5	60		7/6	M3/M3	161	Ja		
6035-65 B6	5.5	65		7/6	M3/M3	165	Ja		
6035-70 B6	5.5	70		7/6	M3/M3	168	Ja		
6035-75 B6	5.5	75		7/6	M3/M3	171	Ja		
6035-80 B6	5.5	80		7/6	M3/M3	174	Ja		
6035-85 B6	5.5	85		7/6	M3/M3	178	Ja		
6035-90 B6	5.5	90		7/6	M3/M3	182	Ja		
6035-95 B6	5.5	95		7/6	M3/M3	186	Ja		
6035-100 B6	5.5	100		7/6	M3/M3	189	Ja		