



Werkstoff: Messing, vernickelt  
 Längentoleranz:  $\pm 0,1$  mm  
 Zwischenlängen: ab 1000 Stück

\* : O = ab Lager, X = ab 1000 Stück, PG = Preisgruppe

Type	SW	L	C 1- C 2	G 1- G 2	PG *	*
6140-05	7	5	5	M 4	084	O
6140-06	7	6	6	M 4	088	O
6140-07	7	7	7	M 4	088	O
6140-08	7	8	8	M 4	088	O
6140-08,5	7	8,5	8,5	M 4	091	O
6140-09	7	9	9	M 4	091	O
6140-10	7	10	10	M 4	091	O
6140-11	7	11	11	M 4	094	O
6140-12	7	12	12	M 4	094	O
6140-13	7	13	13	M 4	097	O
6140-13,5	7	13,5	13,5	M 4	097	O
6140-14	7	14	14	M 4	097	O
6140-15	7	15	15	M 4	097	O
6140-16	7	16	16	M 4	101	O
6140-17	7	17	17	M 4	101	O
6140-18	7	18	9	M 4	101	O
6140-19	7	19	9	M 4	109	X
6140-20	7	20	10	M 4	109	O
6140-21	7	21	10	M 4	120	X
6140-22	7	22	10	M 4	120	O
6140-23	7	23	10	M 4	120	X
6140-24	7	24	10	M 4	120	X
6140-25	7	25	10	M 4	120	O
6140-26	7	26	10	M 4	126	X
6140-27	7	27	10	M 4	126	X
6140-28	7	28	10	M 4	126	O
6140-29	7	29	10	M 4	126	X
6140-30	7	30	10	M 4	126	O
6140-31	7	31	10	M 4	132	X
6140-32	7	32	10	M 4	132	X
6140-33	7	33	10	M 4	132	X
6140-34	7	34	10	M 4	132	X
6140-35	7	35	10	M 4	132	O
6140-36	7	36	10	M 4	142	X
6140-37	7	37	10	M 4	142	X
6140-38	7	38	10	M 4	142	X
6140-39	7	39	10	M 4	142	X
6140-40	7	40	10	M 4	142	O
6140-41	7	41	10	M 4	148	X
6140-42	7	42	10	M 4	148	X
6140-43	7	43	10	M 4	148	X
6140-44	7	44	10	M 4	148	X
6140-45	7	45	10	M 4	148	O

Type	SW	L	C 1- C 2	G 1- G 2	PG *	*
6140-46	7	46	10	M 4	153	X
6140-47	7	47	10	M 4	153	X
6140-48	7	48	10	M 4	153	X
6140-49	7	49	10	M 4	153	X
6140-50	7	50	10	M 4	153	O

526690

526703

526717

526720

526738

Werkstoff: Messing, vernickelt  
 Längentoleranz:  $\pm 0,1$  mm  
 Zwischenlängen: ab 1000 Stück

\* : O = ab Lager, X = ab 1000 Stück, PG = Preisgruppe

Type	SW	L	C	B	G 1- G 2	PG *	*
6040-05	7	5	2,5	8	M 4	094	O
6040-06	7	6	3	8	M 4	099	O
6040-07	7	7	3	8	M 4	099	O
6040-08	7	8	4	8	M 4	099	O
6040-09	7	9	5	8	M 4	105	O
6040-10	7	10	5	8	M 4	105	O
6040-11	7	11	6	8	M 4	112	O
6040-12	7	12	6	8	M 4	112	O
6040-13	7	13	7	8	M 4	113	O
6040-13,5	7	13,5	7	8	M 4	113	O
6040-14	7	14	8	8	M 4	113	O
6040-15	7	15	8	8	M 4	113	O
6040-16	7	16	8	8	M 4	124	X
6040-17	7	17	8	8	M 4	124	X
6040-18	7	18	8	8	M 4	124	O
6040-19	7	19	8	8	M 4	127	X
6040-20	7	20	10	8	M 4	127	O
6040-21	7	21	10	8	M 4	131	X
6040-22	7	22	10	8	M 4	131	X
6040-23	7	23	10	8	M 4	131	X
6040-24	7	24	10	8	M 4	131	X
6040-25	7	25	10	10	M 4	131	O
6040-26	7	26	10	10	M 4	137	X
6040-27	7	27	10	10	M 4	137	X
6040-28	7	28	10	10	M 4	137	X
6040-29	7	29	10	10	M 4	137	X
6040-30	7	30	10	10	M 4	137	O
6040-31	7	31	10	10	M 4	144	X
6040-32	7	32	10	10	M 4	144	X
6040-33	7	33	10	10	M 4	144	X
6040-34	7	34	10	10	M 4	144	X
6040-35	7	35	10	10	M 4	144	O
6040-36	7	36	10	10	M 4	154	X
6040-37	7	37	10	10	M 4	154	X
6040-38	7	38	10	10	M 4	154	X
6040-39	7	39	10	10	M 4	154	X
6040-40	7	40	10	10	M 4	154	O
6040-41	7	41	10	10	M 4	156	X
6040-42	7	42	10	10	M 4	156	X
6040-43	7	43	10	10	M 4	156	X
6040-44	7	44	10	10	M 4	156	X
6040-45	7	45	10	10	M 4	156	O
6040-46	7	46	10	10	M 4	161	X

Type	SW	L	C	B	G 1- G 2	PG *	*
6040-47	7	47	10	10	M 4	161	X
6040-48	7	48	10	10	M 4	161	X
6040-49	7	49	10	10	M 4	161	X
6040-50	7	50	10	10	M 4	161	O