



## ATEX adaptor, PG-metric

## ATEX Adapter, PG-metrisch



Form B



Form A



**Explosion protection:** II 2 G Ex e II

II 2 D Ex tD A21 IP66

**Certificates:** PTB 04 ATEX 1040 X

**Protection class to EN 60 529:** IP 66

**Temperature range:** -20°C to 70°C

**Material:** Polyamide, reinforced glass fibre

**Explosionsschutz:** II 2 G Ex e II

II 2 D Ex tD A21 IP66

**Bescheinigungen:** PTB 04 ATEX 1040 X

**Schutzart gemäß EN 60 529:** IP 66

**Einsatztemperatur:** -20°C bis 70°C

**Material:** Polyamid, glasfaserverstärkt

Type	WISKA-No. RAL 9005 ■ 100.						TL	Form
			mm	mm	mm	mm	mm	
EX-APM 7/12	64748	25	PG 7	M 12	9	16	27	A
EX-APM 7/16	64749	25	PG 7	M 16	9	20	27	A
EX-APM 9/12	64750	25	PG 9	M 12	9	20	27	A
EX-APM 9/16	64751	25	PG 9	M 16	9	20	27	A
EX-APM 9/20	64752	25	PG 9	M 20	9	24	27	A
EX-APM 11/16	64753	25	PG 11	M 16	9	22	27	A
EX-APM 11/20	64754	25	PG 11	M 20	9	24	27	A
EX-APM 11/25	64755	25	PG 11	M 25	9	29	27	A
EX-APM 13,5/16	64756	25	PG 13,5	M 16	10	24	28	A
EX-APM 13,5/20	64757	25	PG 13,5	M 20	10	24	28	A
EX-APM 13,5/25	64758	25	PG 13,5	M 25	10	29	28	A
EX-APM 16/20	64759	25	PG 16	M 20	10	27	28	A
EX-APM 16/25	64760	25	PG 16	M 25	10	29	28	A
EX-APM 16/32	64761	25	PG 16	M 32	10	36	28	A
EX-APM 21/20	64762	10	PG 21	M 20	12	33	19	B
EX-APM 21/25	64763	10	PG 21	M 25	12	33	30	A
EX-APM 21/32	64764	10	PG 21	M 32	12	36	30	A
EX-APM 21/40	64765	10	PG 21	M 40	12	46	30	A
EX-APM 29/20	64766	10	PG 29	M 20	12	42	19	B
EX-APM 29/25	64767	10	PG 29	M 25	12	42	19	B
EX-APM 29/32	64768	10	PG 29	M 32	12	42	19	B
EX-APM 29/40	64769	10	PG 29	M 40	12	46	30	A
EX-APM 29/50	64770	10	PG 29	M 50	12	55	30	A

KUNSTSTOFF  
PLASTIC

MEMBRAN  
MEMBRANE

MESSING  
BRASS

DIN 89280

EDELSTAHL  
STAINL.-STEEL

EMV  
EMC

ATEX  
ATEX

VentGLAND

DICHTUNGEN  
SEALINGS

WERKZEUGE  
TOOLS

TECHNIK  
TECHNICS

INDEX  
INDEX