



Größe	∅D	L	Artikelnr.
M 12 x 1,5	7,2	7	5411 3000
M 16 x 1,5	10	8	5411 3010
M 20 x 1,5	13,2	8,4	5411 3020
M 25 x 1,5	17,2	9,5	5411 3030
M 32 x 1,5	21,2	12	5411 3040
M 40 x 1,5	28,2	14,5	5411 3050
M 50 x 1,5	35,8	18	5411 3060
M 63 x 1,5	45,6	20	5411 3070

Temperaturbereich: -30°C bis +100°C
temperature range: -30°C bis +100°C

②

Toleranzen / tolerances: DIN		Werkstoff / material: CR		Oberfläche / surface		Gewicht / weight:		Volumen / volume:		Farbe / color: RAL9005			
Bearb. / edited		Datum / date		Name / name		Geprüft / checked		Datum / date		Name / name			
		17.11.99		M. Schmid				21.05.07		D. Müller			
Projektion / projection: 		Maßstab / scale: 1:1 (M40)		Benennung / name: SKINTOP DV-M Daten und Montageblatt <i>SKINTOP DV-M technical data sheet</i>									
02		muellerd 22.07.2008		U.I. Lapp GmbH		Zeichnungs-Nr. / drawing no.: BS99_2434				Blatt / sheet: 1/1		Dok. Art / doc. type: LDM	
Ind. vs		Änderungs-Nr. / change number		Datum / date		Bearb./edited		Gepr./check.		Ersatz für / substitute for: BS99_2434-1			
										DIN A 4			