



Größe	∅D	L	Artikelnr.
M 12 x 1,5	7,2	7	5411 3000
M 16 x 1,5	10	8	5411 3010
M 20 x 1,5	13,2	8,4	5411 3020
M 25 x 1,5	17,2	9,5	5411 3030
M 32 x 1,5	21,2	12	5411 3040
M 40 x 1,5	28,2	14,5	5411 3050
M 50 x 1,5	35,8	18	5411 3060
M 63 x 1,5	45,6	20	5411 3070

Temperaturbereich: -30°C bis +100°C  
temperature range: -30°C bis +100°C

②

Toleranzen / tolerances: DIN		Werkstoff / material: CR		Oberfläche / surface		Gewicht / weight:		Volumen / volume:		Farbe / color: RAL9005	
Bearb. / edited		Datum / date		Name / name		Geprüft / checked		Datum / date		Name / name	
		17.11.99		M. Schmid				21.05.07		D. Müller	
Projektion / projection:		Maßstab / scale:		Benennung / name:							
		1:1 (M40)		SKINTOP DV-M Daten und Montageblatt SKINTOP DV-M technical data sheet							
02		muellerd 22.07.2008		U.I. Lapp GmbH		Zeichnungs-Nr. / drawing no.:		BS99_2434		Blatt / sheet: 1/1	
Ind. vs		Änderungs-Nr. / change number		Datum / date		Gepr. / check.		Ersatz für / substitute for: BS99_2434-1		Dok. Art / doc. type: LDM DIN A 4	