



Größe	∅D	L	Artikelnr.
M 12 x 1,5	7,2	7	5411 3000
M 16 x 1,5	10	8	5411 3010
M 20 x 1,5	13,2	8,4	5411 3020
M 25 x 1,5	17,2	9,5	5411 3030
M 32 x 1,5	21,2	12	5411 3040
M 40 x 1,5	28,2	14,5	5411 3050
M 50 x 1,5	35,8	18	5411 3060
M 63 x 1,5	45,6	20	5411 3070

Temperaturbereich: -30°C bis +100°C
temperature range: -30°C bis +100°C

②

Toleranzen / tolerances: DIN		Werkstoff / material: CR		Oberfläche / surface		Gewicht / weight:		Volumen / volume:		Farbe / color: RAL9005		
Bearb. edited	Datum / date 17.11.99	Name / name M. Schmid		Geprüft checked	Datum / date 21.05.07	Name / name D. Müller		Maßangaben in dimension units mm				
Projektion / projection: 		Maßstab / scale: 1:1 (M40)		Benennung / name: SKINTOP DV-M Daten und Montageblatt <i>SKINTOP DV-M technical data sheet</i>								
02		muellerd	22.07.2008	U.I. Lapp GmbH		Zeichnungs-Nr. / drawing no.: BS99_2434			Blatt sheet: 1/1	Dok. Art doc. type LDM		
Ind. vs	Änderungs-Nr. change number	Datum / date Bearb./edited	Gepr./check.	Ersatz für / substitute for: BS99_2434-1								DIN A 4