



| Größe      | ∅D   | L    | Artikelnr. |
|------------|------|------|------------|
| M 12 x 1,5 | 7,2  | 7    | 5411 3000  |
| M 16 x 1,5 | 10   | 8    | 5411 3010  |
| M 20 x 1,5 | 13,2 | 8,4  | 5411 3020  |
| M 25 x 1,5 | 17,2 | 9,5  | 5411 3030  |
| M 32 x 1,5 | 21,2 | 12   | 5411 3040  |
| M 40 x 1,5 | 28,2 | 14,5 | 5411 3050  |
| M 50 x 1,5 | 35,8 | 18   | 5411 3060  |
| M 63 x 1,5 | 45,6 | 20   | 5411 3070  |

Temperaturbereich: -30°C bis +100°C  
temperature range: -30°C bis +100°C

②

|                                 |                                |                                  |                    |   |                          |   |  |                   |                        |                              |  |         |
|---------------------------------|--------------------------------|----------------------------------|--------------------|---|--------------------------|---|--|-------------------|------------------------|------------------------------|--|---------|
| Toleranzen / tolerances:<br>DIN |                                | Werkstoff / material:<br>CR      |                    | Oberfläche / surface  |                          | Gewicht / weight:                                 |  | Volumen / volume: |                        | Farbe / color:<br>RAL9005    |  |         |
| Bearb.<br>edited                | Datum / date<br>17.11.99       | Name / name<br>M. Schmid         | Geprüft<br>checked | Datum / date<br>21.05.07  | Name / name<br>D. Müller | Maßangaben in mm                                  |  |                   |                        |                              |  |         |
| Projektion / projection:<br>    |                                | Maßstab / scale:<br>1:1<br>(M40) |                    | Benennung / name:<br><b>SKINTOP DV-M Daten und Montageblatt</b><br><i>SKINTOP DV-M technical data sheet</i> |                          |   |  |                   |                        |                              |  |         |
| 02                              |                                | muellerd                         | 22.07.2008         | <b>U.I. Lapp GmbH</b><br><small>LAPP GROUP</small>  |                          | Zeichnungs-Nr. / drawing no.:<br><b>BS99_2434</b> |  |                   | Blatt<br>sheet:<br>1/1 | Dok. Art<br>doc. type<br>LDM |  |         |
| Ind.<br>vs                      | Änderungs-Nr.<br>change number | Datum / date<br>Bearb./edited    | Gepr./check.       | Ersatz für / substitute for: BS99_2434-1  |                          |   |  |                   |                        |                              |  | DIN A 4 |