



TYPE	A	B
B-3	70±0.5	80 <sup>+1</sup> <sub>0</sub>
CHM-3	100±0.5	110 <sup>+1</sup> <sub>0</sub>
DH-3	130±0.5	140 <sup>+1</sup> <sub>0</sub>
FM-3	190±0.5	200 <sup>+1</sup> <sub>0</sub>