


BCT-TYPE



型號 Item No.	L	L1	W	W1	H
BCT-127	127±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-152	152±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-201	201±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-266	266±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-300	300±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-362	362±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-521	521±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-679	679±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-838	838±7	11.4±0.5	4.6±0.1	6.4±0.5	4.1±0.5
BCT-127L	127±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-152L	152±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-201L	201±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-266L	266±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-300L	300±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-362L	362±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-521L	521±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-679L	679±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5
BCT-838L	838±7	13.8±0.5	7.9±0.1	10±0.5	5.2±0.5

MATERIAL 304 SS

ITEM NO.

BCT-TYPE

SCALE

FINISH

NAME

STAINLESS STEEL CABLE TIE



(. .)

TOLERANCE
AS FIGURE



(. .)
03-05-2009
DATE

REVISIONS

K001

R.NO.

