

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES, UNLESS OTHERWISE SPECIFIED:

STS2 TOOL FOR INSTALLER CONTROLLED TENSIONING AND FLUSH CUT-OFF OF EXCESS CABLE TIE.



FOR USE WITH MINIATURE, INTERMEDIATE, AND STANDARD PANDUIT CABLE TIES WITH WIDTHS FROM .10 TO .19.

COLOR: BLACK WITH BLACK HANDLE.

WEIGHT: 2-1/2 OZ (71 GRAMS)

ROTATION FOR CUTOFF: 90°

NO MAINTENANCE: NO REPAIR



CAD FILENAME/LAYERS		R19333AA_WE19333B01_00	
PANDUIT		CORP TINLEY PARK, ILLINOIS	
CUSTOMER DWG, STS2			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
(.X) ± .01		(.XXX) ± .005	
(.XX) ± .005		ANGLES ± .01	
DRAWN BY	B.D.	MAT'L:	NONE
DATE	2-18-93	SCALE	NONE
CHK'D		DRAWING NO.	WE19333B01
		DWG SIZE	B

00	2-18-93	BAD	MMM	RELEASED	3152	-	MMM					
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP				