



**Sondertyp:**

**T6,8K  
(6,8 x 22 mm)**

**auf Anfrage lieferbar !**

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...
6V	20mA	0,12W	<b>00540620</b>	345000
	50mA	0,3W	<b>00540650</b>	345017
	80mA	0,48W	<b>00540680</b>	345024
	200mA	1,2W	<b>00540618</b>	345031
12V	20mA	0,24W	<b>00541220</b>	345048
	40mA	0,48W	<b>00541240</b>	345314
	50mA	0,54W	<b>00541250</b>	345055
	100mA	1,2W	<b>00541210</b>	345062
24V	20mA	0,5W	<b>00542420</b>	345079
	25mA	0,6W	<b>00542425</b>	345086
	40mA	1,0W	<b>00542440</b>	345093
	50mA	1,2W	<b>00542450</b>	345109
	80mA	2,0W	<b>00542480</b>	345116
28V	40mA	1,12W	<b>00542840</b>	345123
	45mA	1,26W	<b>00542845</b>	345130
	50mA	1,4W	<b>00542850</b>	345352
30V	20mA	0,6W	<b>00543020</b>	345284
	40mA	1,2W	<b>00543040</b>	345147
	50mA	1,5W	<b>00543050</b>	345154
	100mA	3,0W	<b>00543010</b>	345161
36V	20mA	0,72W	<b>00543620</b>	345178
	33mA	1,2W	<b>00543633</b>	345369
Grün	40mA	1,44W	<b>00543640</b>	345321
	40mA	1,44W	<b>00543640-G</b>	345376
	50mA	1,8W	<b>00543650</b>	345185
48V	20mA	1,0W	<b>00544820</b>	345192
	25mA	1,2W	<b>00544825</b>	345208
	40mA	1,4W	<b>00544840</b>	345215
	50mA	2,0W	<b>00544850</b>	345222
60V	20mA	1,2W	<b>00546020</b>	345239
	40mA	2,4W	<b>00546040</b>	345246
	60mA	3,6W	<b>00546060</b>	345338
70V	20mA	1,4W	<b>00547020</b>	345253
80V	20mA	1,6W	<b>00548020</b>	345345
<b>Glimmlampe mit Widerstand</b>				
230V			<b>00542222</b>	345260
<b>Glimmlampe mit Widerstand grün</b>				
230V			<b>00542223</b>	345277
<b>Lampenzieher T2</b>			<b>01909005</b>	

Abweichende Spannungen und Leistungen auf Anfrage lieferbar (VPE 100 Stück) !