



Die fettgedruckten Typen kommen in Leuchtmeldern und Leuchttastern aller namhaften Hersteller zum Einsatz

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553....
6V	50mA	0,3W	<b>00210650</b>	100647
	75mA	0,45W	<b>00210675</b>	100654
	100mA	0,6W	<b>00210610</b>	100661
	180mA	1,1W	<b>00210618</b>	100012
	300mA	1,8W	<b>00210630</b>	100982
	333mA	2,0W	<b>00210602</b>	100029
	500mA	3,0W	<b>00210603</b>	100036
	830mA	5,0W	<b>00210605</b>	100043
	1000mA	6,0W	<b>00210606</b>	100050
6,3V	320mA	2W	<b>00210632</b>	100999
6-7V		2,0W	<b>00210702</b>	100364
7V	100mA	0,7W	<b>00210710</b>	100852
	300mA	2,1W	<b>00210730</b>	100678
8V	320mA	2,24W	<b>00210722</b>	100937
	100mA	0,8W	<b>00210808</b>	100456
9V	300mA	2,4W	<b>00210830</b>	100685
	450mA	4,0W	<b>00210945</b>	100500
10V	50mA	0,5W	<b>00211050</b>	100692
	100mA	1,0W	<b>00211001</b>	100708
	200mA	2,0W	<b>00211020</b>	100715
12V	50mA	0,6W	<b>00211250</b>	100470
	100mA	1,2W	<b>00211210</b>	100869
	120mA	1,44W	<b>00211212</b>	100067
	165mA	2,0W	<b>00211202</b>	100074
	200mA	2,4W	<b>00211220</b>	100876
	250mA	3,0W	<b>00211203</b>	100081
12-15V	417mA	5,0W	<b>00211205</b>	100098
		2,0W	<b>00211502</b>	100371
14V	80mA	1,12W	<b>00211480</b>	100838
	200mA	2,8W	<b>00211420</b>	090450
15V	50mA	0,75W	<b>00211550</b>	100722
	100mA	1,5W	<b>00211510</b>	100739
	200mA	3,0W	<b>00211520</b>	100746
18V	100mA	1,8W	<b>00211810</b>	100753
	170mA	3W	<b>00211817</b>	090467
24V	20mA	0,5W	<b>00212420</b>	100487
	40mA	1,0W	<b>00212440</b>	100883
	50mA	1,2W	<b>00212450</b>	100104
	60mA	1,5W	<b>00212460</b>	100890
	<b>80mA</b>	<b>2,0W</b>	<b>00212408</b>	100111
	100mA	2,4W	<b>00212410</b>	100524
	125mA	3,0W	<b>00212403</b>	100128
	160mA	4,0W	<b>00212404</b>	100906
208mA	5,0W	<b>00212405</b>	100135	
24-30V		<b>2,0W</b>	<b>00213002</b>	100388
		4,0W	<b>00213014</b>	100395
<b>Lampenzieher T3<sup>1</sup>/<sub>4</sub></b>			<b>01909007</b>	